

LED workplace light Floodlight

With and without dimmer



Execution:

- LED light, with flexible light arm, rubber-coated
- Low power consumption and low heat generation
- Solid and robust design for heavy-duty use
- High-performance chip with lamp life of min. 50,000 operating hours
- Anti-glare and flicker-free light, low reflection, with 24 V power supply
- Luminous flux: 1200 lumen, colour temperature: daylight white, approx. 5500 Kelvin, 160 degree uniform illumination
- 88-mm magnetic base with 420 N adhesive force
- Total length 850 mm, light head 175 x 50 x 25 mm
- Ref. no. 160: No dimmer
- Ref. no. 162: With dimmer (continuously variable)

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



Art. no.	56879 160
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/43
Power rating	10 W
Arm length	700 mm
IP protection class	IP 65
Dimmable	No
Gross Weight	1.528 kg
Product Group	5ID

EAN

4260131235887