


PXF4053 Datasheet

Product Name // No Cable, Rear panel mount fiber connector

 [View Product Page](#)



// Product Description:

- ⬢ Rear Panel Mount Fiber Connector
 - ⬢ Sealed to IP66, IP68, IP69K when mated with compatible connector
 - ⬢ no cable options, or pre-terminated 1M available
 - ⬢ Simplex LC type fiber connector
- ⬢ Choices of OS1, OM1 and OM3 cables for single or multimode
 - ⬢ PXP4083 Sealing Cap available separately to maintain IP rating of unmated connectors
 - ⬢ Mate with flex fiber connector PXF4050

// General Information:

Product Display Title:	Rear Panel Mount Fiber Connector
Product Family:	Circular Fiber Connectors
Product Series:	4000 Series - Simplex LC Fiber Buccaneer
Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
Contact Type:	LC Fiber
Coupling Type:	30 Degree coupling
Diameter Over Coupling Ring Mm:	19.7mm
Fibre Mode:	OS1
Flamability Rating:	UL94V-0
Function:	Rear Panel Mount to LC Connector Double Ended Fiber Cable
Ip Rating:	IP66, IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	-20°C

// Product PDF Links



// Product 3D CAD Model Links



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)