

Slides DZ 3932 EC, Width 12.7 mm, to 68 kg, Full Extension

Material:

Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Plastic / zinc-plated steel. Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Self Close.
- Fast disconnection.
- Hold-in in closed position.
- Service life 50,000 cycles.
- Temperature range: -10°C to +40°C.



Accuride

Ordering details: e.g.: Prod. No. 649 044 30, Slides DZ 3932 EC



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	Load Rating per Pair kg	Weight per Pair kg
649 044 30	300	275	-	96	-	-	192	-	-	35	1,18
649 044 35	350	350	128	-	-	-	128	224	-	35	1,40
649 044 40	400	400	128	192	-	-	160	288	-	50	1,64
649 044 45	450	450	128	256	-	-	160	320	-	50	1,88
649 044 50	500	500	128	224	288	-	192	384	-	60	2,09
649 044 55	550	550	128	224	352	-	224	416	-	60	2,32
649 044 60	600	600	128	224	352	-	256	480	-	68	2,56
649 044 65	650	650	128	224	352	448	256	512	-	68	2,78
649 044 70	700	700	128	224	352	480	256	448	576	68	3,01

* Not available for slide length 300 mm.

** Not available for slide length 350 mm.

*** Not available for slide length 400 mm.

Note

Recommended mount: M4 screw/6mm Euro screw/4mm wood screw. Max. head. height 2,5mm/Ø9,6mm.

Use all mounting positions to achieve the max. load rating.

Attention: Vertical (side) mounting only.

The load capacity was tested at a slide spacing of 450mm.

For optimal performance, the construct drawer width must be 27 mm less than the cabinet opening width.