




## BNC AL 0,64

Industrial Connectors:Measuring and Testing Equipment:Measuring leads:0,64 mm system

### Product description

Description	BNC adapter lead with insulated sockets for 0.64 mm round pillar and 0.64 mm rectangular pillar. Red inner lead, black shielding; cable type RG 58 A/U, 50 Ohm. For use with oscilloscopes, PC cards, etc
Type	BNC AL 0,64
Order No.	933 844-001
System	0.64 mm system
Cable length	120 cm BNC and 10 cm wire
Cable color	black
Housing Color	black

### Drawing



### Technical data

Pin dimensions	0.64 mm
Type of contact	socket
Type of termination	BNC, 2 x 0.64 mm diameter socket
Cable specification	highly flexible lead
Rated voltage	DC 60 V

### Environmental conditions

Temperature range	-15 °C to +70 °C
-------------------	------------------