

TOLEDO BALL

ToLEDo Ball V7 470LM 865 E14 SL

0029627



Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent ball lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- 15,000 hours average rated life



PRODUCT OVERVIEW

Product name	ToLEDo Ball V7 470LM 865 E14 SL
Technology	LED
Watt (Rated) (W)	4.5
Type	LED exchangeable
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4741013
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Wattage (W)	4.5
Product Voltage (V)	230
Dimmable	No
Average life (Nominal) (h)	15000
Product EAN number	5410288296272

DATA TABLE

General data

TOLEDO BALL

ToLEDo Ball V7 470LM 865 E14 SL

0029627

Product name	ToLEDo Ball V7 470LM 865 E14 SL
Technology	LED
Watt (Rated) (W)	4.5
Type	LED exchangeable
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4741013
Warranty	3 years

Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	4.5
Equivalent watt (W)	40
Product Voltage (V)	230
Control gear required	No
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	No
Inrush Current (A)	2.4
Inrush Duration (µs)	420
Lamp Energy Label (class)	F
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 16A C Breaker	67
Max. Luminaires per 16A B Breaker	33

Lifetime data

Lifespan L70 B50	15000
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	82
Nominal Product Diameter (mm)	45
Weight (kg)	0.018

TOLEDO BALL

ToLEDo Ball V7 470LM 865 E14 SL

0029627


Packaging

Single packaging type	Carton
Product EAN number	5410288296272
Packaging single length / height (cm)	5.0
Packaging single width (cm)	5.0
Packaging single depth (cm)	9.5
DUN14 (outer)	15410288296279
Units per outer package	6
Packaging outer length / height (cm)	15.8
Packaging outer width (cm)	10.7
Packaging outer depth (cm)	10.2


Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

PHOTOMETRY



TECHNICAL DRAWINGS



SYLVANIA


TOLEDO BALL

ToLEDo Ball V7 470LM 865 E14 SL
0029627



SYLVANIA

0029627



5
kWh/1000h



2019/2015


SYLVANIA

TOLEDO BALL

ToLEDo Ball V7 470LM 865 E14 SL
0029627



0029627



5
kWh/1000h



2019/2015