

Hammer drill GBH 5-40 DCE SDS-max Professional

1150 watt

BOSCH

Application:

For drilling and chiselling with pneumatic impact mechanism, in stone and concrete.

Execution:

- Overload coupling
- Vibration Control vibration damping
- speed preselection
- ball joint for preventing cable breakage
- Turbo-Power function for extra power when chipping
- Automatic switch lock
- service display and standby display

Advantage:

- clutch claws unlock and torque is minimised to prevent the tool blocking abruptly

Delivery:

Grease tube, machine cloth, additional handle, in tool case



Art. no.	70170 091
Brand	BOSCH
Manufacturer Part Number	0611264000
Model	GBH 5-40 DCE
Manufacturer Article Number	0611264000
Battery included	No
Max. impact energy	8.8 J
Max. impact rate	3050 rpm
Min./max. impact rate	1500-3050 rpm
Power input	1150 W
Max. recommended drilling diameter in concrete	40 mm
Max. core drill bit diameter	90 mm
Weight	6.8 kg
With rubber-coated handle	Yes
With electronic feedback	Yes
With soft start	No
With chisel function	Yes
With reverse switch off	No
With restart protection	No
Gross Weight	11.100 kg
Product Group	731

EAN

3165140461214