

SR255S0HIHSUVX2



Article Number: 115-42002

Releasable Cable Tie, 14.6" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number SR255S0HIHSUVX2

Type SR255S

Color Black (BK)

- Features and Benefits**
- High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.
 - Special design offers a release feature for quick and easy access to wire bundles.
 - Head design provides high tensile strength with very low insertion force even after repeated use.

Product Description HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, 14.6" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 250.0 lbs

Minimum Tensile Strength (Metric) 1115.0 N

Length L (Imperial) 8.9 "

Length L (Metric) 225.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure Yes

Width W (Imperial) 0.5 "

Width W (Metric) 12.6 mm

Cable Tie Width Max. (Imperial) 0.49 "

Cable Tie Width Max. (Metric) 12.5 mm

Bundle Diameter Min. (Imperial) 0.51 "

Bundle Diameter Min. (Metric) 13.0 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 25

Carton Quantity 1000

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
ROHS Compliant	Yes