

PRODUCT SPECIFICATION

D03003

Adjustable Torque Screwdriver

EN#:4711552156225

**Safety and environmental protection :**

- RoHS & Pb free: RoHS

Material :

- Material of hex drive: Chrome vanadium steels SAE(AISI) 6140
- Material of adjustment ring & body: Aluminum alloy
- Material of handle: NBR Rubber

Specifications :

- Length (mm): 180
- Specification of torque (Nm): 0.1~1.2Nm
- Specification of torque (lbf-in): 1.33~10.18 lbf-in
- Graduation(N-M): 0.01
- Tolerance of torque (%): $\pm 6\%$
- Dimension of ratchet: 1/4" (6.35mm)

Product Weight (w/o package)(g)	Measurement		
	L(mm)	W(mm)	H(mm)
225.4	180	36	36

Individual Packing :

Master Packing :

	Pieces	N.W.(Kg)	G.W.(Kg)	Measurement			Cuft
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.32	23	7	7	-
Inner box	1	0	0	0	0	0	0
CTN	24	7.68	8.51	50.9	25.8	20.3	0.94