

## Shoulder milling cutter VSM890™

For indexable milling inserts SN.X 1204..



### Application:

The WIDIA™ Victory™ angular milling cutter VSM890™-12 guarantees precise 90-degree shoulders and offers maximum economy with eight effective cutting edges per indexable insert. With an axial cutting depth of up to 8.0 mm, the tool also guarantees high productivity.

### Execution:

- Double-sided, robust indexable insert with 8 cutting edges
- Highly positive geometry for lower cutting forces
- Integrated facing chamfer for excellent surface quality
- Internal cooling

### Advantage:

- True 90° surfaces
- Enables cutting depths of up to 9.8 mm
- Low burr formation



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>16044 236</b> |
| <b>Brand</b>                    | WIDIA            |
| <b>Manufacturer Part Number</b> | 6596121          |
| <b>Cutting edge diameter</b>    | 125 mm           |
| <b>Length</b>                   | 63 mm            |
| <b>Bore diameter</b>            | 40 mm            |
| <b>max. ap</b>                  | 9.8 mm           |
| <b>Number of cutting edges</b>  | 14 PCS           |
| <b>Gross Weight</b>             | 2.850 kg         |
| <b>Product Group</b>            | 1XJ              |

### EAN

4061779073639