


Y-splitter

ZDO2H030VAS0000-00STGH040VAS



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	< 250 AC / < 300 DC
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	4

Operating conditions

Ambient temperature	[°C]	-25...100
Protection		IP 65; IP 67; IP 68; IP 69K

Mechanical data

Weight	[g]	33
Materials		Housing: PA Halogen-free; Sealing: EPDM
Material nut		stainless steel (1.4404 / 316L) / stainless steel (1.4404 / 316L)

Remarks

Pack quantity	1 pcs.
---------------	--------

Y-splitter


ZDO2H030VAS0000-00STGH040VAS

Electrical connection - plug



Electrical connection

Connection



connection to IEC 61076-2-101

Electrical connection - socket



Electrical connection - plug

Connector: 1 x M12; Moulded body: PA, Halogen-free; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.2 Nm

EBF006



Y-splitter

ZDO2H030VAS0000-00STGH040VAS

Electrical connection - socket

Connector: 2 x M12; Moulded body: PA, Halogen-free; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm