

## Clamping screw sets



### Execution:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

### Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



<b>Art. no.</b>	<b>26209 165</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	83022
<b>Suitable for groove width</b>	16 mm
<b>Thread dimension</b>	M16
<b>Number of DIN 787 T-slot screws</b>	2 x M16 x 63 mm, 4 x M16 x 100 mm, 4 x M16 x 160 mm
<b>Number of DIN 6379 stud bolts (extension pin)</b>	4 x M16 x 80 mm, 4 x M16 x 125 mm, 4 x M16 x 250 mm
<b>Number of DIN 6330 B high nuts</b>	4 PCS
<b>Number of extension nuts</b>	4 PCS
<b>Wooden box length</b>	339 mm
<b>Wooden box width</b>	294 mm
<b>Wooden box height</b>	48 mm
<b>Gross Weight</b>	7.430 kg
<b>Product Group</b>	260

### EAN

4020772083021