

Angular milling cutter 90°

For indexable milling insert WNEU 0403.

ATORN®

Application

Powerful angular milling cutter with particularly economic, double-sided reversible tip with 6 cutting edges. Flexible use for multiple machining steps, such as face, angular, trim and groove milling.

Version

- Wear-resistant, nickel-plated version
- Internal cooling

Advantage

- 6 cutting edges on double-sided indexable insert
- special chip breaker geometry enables low power consumption
- Large plate thickness for optimum process reliability
- Optimised plane cutting edge for high surface quality



Art. No.	16020 840
Cutting edge diameter	40 mm
Length	40 mm
Bore diameter	16 mm
max. ap	3.5 mm
Number of cutting edges	6 PCS

EAN-Code

4050293534863