

Sphygmomanometers and Stethoscopes

SHOCKPROOF, LATEX-FREE SPHYGMOMANOMETERS

The innovative HEINE GAMMA G series of latex-free aneroid sphygmomanometers offers top-quality and functionality with unmatched value for money. Highest precision and durability combined with a functional, modern design guarantee you long-term reliability in clinic and practice.

Clinical Approval




HEINE GAMMA G Sphygmomanometers are now clinically-validated under the European Union protocol on hypertension. The validation confirms the long-term accuracy of measurement of systolic and diastolic blood pressure.

Stethoscopes for precise auscultation.

HEINE GAMMA Series 3 stethoscopes are perfectly adapted to everyday use. Major improvements in acoustic performance increase the precision with which heart, lung and vascular sounds can be heard.







SHOCKPROOF

[01] Shockproof double-walled construction with unique manometer protection. The robust double-walled construction with a unique triple manometer mount gives ideal protection against shocks, comfortably exceeding both the European EN1060 and the American SP9 tests.

AIR PRESSURE DISTRIBUTION SYSTEM

[02] Single-tube construction with an innovative air pressure distribution system. The valve construction provides ideal air pressure conditions to absorb pressure peaks in air flow to the manometer during inflation. This advantage was only possible until now with twin-tube systems.

HEINE GAMMA® G7

The model with aluminium alloy construction and precision valve



: Shockproof

: Latex-Free

: Aluminium upper housing

: 10 year warranty

- : Shockproof.
- : Latex-Free.
- : Exclusive Pressure-Distribution System.
- : Pressure-Proof Manometer. Ensures durability and reliability.
- : Micro-Filter. Protects valve and manometer.
- : Large-diameter Scale. 56 mm diameter black-on-white scale is easy to read.
- : High Quality Indicator. Precisely calibrated, durable and shock resistant.
- : Large Insufflation Bulb. 50% larger bulb volume for fast inflation of the cuff.
- : Exclusive Air-Release Valve. Provides fine and precise air release rate adjustment, quick deflation, and extreme durability. A rubber-stop prevents valve-lock.
- : Upper housing made of aluminium alloy with a shock absorbing ring protecting indicator and glass.
- : Lower housing is moulded of shockproof plastic with shock absorbing, anti-slip coating.
- : Light alloy, adjustable Spoon. For both right- or left-handed operation.
- : High quality, single-tube cuff with Velcro Fastener. Washable.
- : Ergonomic Design: G7 is perfectly balanced for comfort and ease of use.
- : 10 year warranty.*

*against defects in manufacture and workmanship for a period of 10 years from the date of purchase.

GAMMA G7	
complete with adult cuff, in zipper pouch	M-000.09.232
complete with child cuff, in zipper pouch	M-000.09.233
Practice Kit with child, adult and small adult cuff in zipper pouch	M-000.09.554
complete with adult cuff without zipper pouch, box of 10	M-000.09.560



HEINE GAMMA® G5

The HEINE standard sphygmomanometer

Combines all the design and quality features of the GAMMA G7, except:

- : Housing is moulded of shockproof plastic with shock absorbing, anti-slip coating.
- : Adjustable Spoon (Polyamid Thermo Plastic). For both right or left-handed operation.
- : 5 year warranty.*

*against defects in manufacture and workmanship for a period of 5 years from the date of purchase.

GAMMA G5	
complete with adult cuff, in zipper pouch	M-000.09.230
complete with child cuff, in zipper pouch	M-000.09.231
Practice Kit with child, adult and small adult cuff in zipper pouch	M-000.09.555
complete with adult cuff without zipper pouch, box of 10	M-000.09.561




: Shockproof

- : Latex-Free
- : Shock-absorbing Polyamid housing

HEINE GAMMA® GP

HEINE standard sphygmomanometer with push-button valve

Combines all the design and quality features of the GAMMA G5, but with a push-button valve:



: 5 year warranty.*

*against defects in manufacture and workmanship for a period of 5 years from the date of purchase.

: Shockproof

- : Latex-Free
- : Shock-absorbing Polyamid housing

GAMMA GP	
complete with adult cuff, in zipper pouch	M-000.09.242
complete with child cuff, in zipper pouch	M-000.09.243
Practice Kit with child, adult and small adult cuff in zipper pouch	M-000.09.556
complete with adult cuff without zipper pouch, box of 10	M-000.09.562



HEINE GAMMA® XXL LF


The top-quality professional model

Since the GAMMA XXL LF is non-mercurial, it is both safe and environmentally-friendly.




- : Durable polycarbonate construction. Will hold up in the busiest hospital and practice environments.
- : Oversized 130 mm Diameter Scale. Can be pivoted for clear, easy reading from any angle.
- : Long Spiral Inflation Tube (3 m). For increased working distance.
- : High Quality Indicator. Precisely-calibrated and durable.
- : Precision Air-Release Valve. Fine and precise air release.
- : Maintenance-free, precise and durable manometer.
- : Mercury-free. Environmentally friendly.
- : Wall, Desk, Rail and Wheeled Stand. Adjustable height.
- : 10 year warranty.*

*against defects in manufacture and workmanship for a period of 10 years from the date of purchase.



Accessories	
Cuff-holder for GAMMA XXL LF-T	M-000.09.141
Desk stand for GAMMA XXL LF-T	M-000.09.142
Adjustable wheeled stand for GAMMA XXL LF-S	M-000.09.145
Universal mounting plate for GAMMA XXL LF-W, -S, -R	M-000.09.306
Rail clamp for GAMMA XXL LF-R	M-000.09.307





: 10 year warranty





Blood-pressure cuffs and accessories

Latex-free blood-pressure cuffs

Cuffs for GAMMA G7/G5/GP/XXL LF sphygmomanometers.



- : Latex-free.
- : Fit the most widely-used sphygmomanometers.
- : High-quality velcro cuffs made of wear-resistant material. Physiologically tested.
- : Double-sewn.
- : Washable.
- : Index mark for exact positioning.
- : Clear indication of size and control mark for arm circumference.
- : Extra-thick, highly-flexible tube. For a long life.
- : Proven reliability. Absolutely airtight system.

	GAMMA G7/G5/GP	Single-t Size	ube cuffs Circumfei	s (cpl.) rence/cm	Single-t Size	ube bladders	Outer cuffs Size	
	Small child	6x28	8-13	M-000.09.700	5x15	M-000.09.661	6x28	M-000.09.059
	Child	10x34	13-20	M-000.09.702	8x20	M-000.09.663	10x34	M-000.09.060
	Small adult	14×53	20-29	M-000.09.704	11x23	M-000.09.664	14×53	M-000.09.061
	Adult	14x58	29-41	M-000.09.619	12x28	M-000.09.665	14×58	M-000.09.055
	Large adult	20x86	>41	M-000.09.615	18x52	M-000.09.667	20x86	M-000.09.057

