


Tree 8TX IP67 Metal - Unmanaged Switch - 8xM12

8 port unmanaged switch

For connection cables please see chapter "Connection Technology"

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Connections

Fieldbus	8 × M12 female, D-coded
Supply System	1 × M12 male, A-coded

Technical Data

Operating voltage	2 × 18...30 V DC, redundancy
Transfer rate	10/100 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

General data

Protection	IP67
------------	------

Housing	Zinc die casting, matte nickel plated
Mounting method	4 hole screw mounting
Temperature range	-25...+60 °C (storage temperature -40...+80 °C)
Dimensions H × W × D	145×55×31 mm

Diagnostic

Communication status	via LED
Monitoring - no voltage	yes

Commercial data

country of origin	DE
customs tariff number	85176200
minimum order quantity	1