

## PDNN clamp holder, neutral

For copy turning and longitudinal turning using DN indexable insert

**ATORN**<sup>®</sup>

### Application


For copy turning and longitudinal turning using DN indexable insert 55°.

### Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type D, 93° pitch angle, 55° tip angle, 0° clearance angle

### Advantage

- very slim geometry, optimised for contour turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



<b>Art. No.</b>	<b>17856 006</b>
<b>ISO name</b>	PDNN N 3232 P15
<b>Shaft height</b>	32 mm
<b>Shank width</b>	32 mm
<b>Length</b>	170 mm
<b>Length of head</b>	34 mm
<b>Programming size</b>	16 mm
<b>Suitable for indexable inserts</b>	DN.. 1506..
<b>Tool design</b>	Neutral
<b>DIN</b>	4983

### EAN-Code

4050293348279