

Cemented carbide angular milling cutter

ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight shank according to DIN 1835 A
- Cutter angles chamfered 0.5 mm x 60° to planing side



Art. no.	16530 240
Brand	ORION
Manufacturer Part Number	16530240
Cutting material	Carbide
Number of cutting edges	6 PCS
Chamfer angle	60 Degree
Tool holding device	HA parallel shank
Cutting edge diameter	40 mm
Width of cutting edge	12 mm
Immersion depth	30 mm
Length	80 mm
Shank diameter	20 mm
Form	C
fz steel 1000	0.05 mm
Gross Weight	0.265 kg
Product Group	165

EAN

4039247104239