

Hydraulic short stroke cylinder RCS



Version:

- Single-acting cylinder
- Without fastening thread on cylinder head and piston rod
- Operating pressure of 700 bar
- With spring return and scraper ring
- Stripping ring
- Piston rod with nickel plating
- Model RCS 1002 with carry handle
- For RCS 101-502 models, the coupling sleeve is inserted at an angle of 5°.

Advantage:

- Retaining ring prevents piston rod from being pushed out

Delivery:

Pressure cylinder with CR400 coupler and fluted pressure fitting.



Art. no.	29511 070
Model	RCS 1002
Max. compressive force	887 kN
Lift height	57 mm
Oil capacity	722 cm ³
Overall height, retracted	141 mm
Outer diameter	165 mm
Weight	20.7 kg