



Pushing Performance  
Since 1945

# M12 A-cod 5-pol an /- f /- PVC 5.00m



Image is for illustration purposes only. Please refer to product description.

Part number	C2 13 200 0000 0006
Specification	M12 A-cod 5-pol an /- f /- PVC 5.00m
HARTING eCatalogue	<a href="https://b2b.harting.com/C213200000000006">https://b2b.harting.com/C213200000000006</a>

## Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Female Angled Overmoulded
Type of cable	Copper cable (round)

## Version

Cable length	5 m
Number of cores	5
Core structure	5x 0.34 mm <sup>2</sup>
Termination method	Crimp termination
Shielding	Unshielded
Coding	A-coding

## Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +80 °C moved -40 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition



**Pushing Performance**  
Since 1945

## Technical characteristics

Cable diameter	5.3 mm
----------------	--------

## Material properties

Material (cable)	PVC
Colour (cable)	RAL 7040 (Window grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	2
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140512849
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line