

Description

The UPS Rackmount range provides stable and reliable power protection with scalable run time it is ideal for PC users or small businesses, as well as for small telecom applications. The UPS Rackmount is compact and provides stable power protection against surges and spikes. Its embedded microprocessor controller guarantees high reliability. It can automatically shut down without any load and restart while AC power is recovering.

Key Features

- Built in AVR
- DC Cold Start
- Audible Alarm
- USB Connectivity
- Intelligent CPU Control
- Wide Input Range
- Software Monitoring included (Serial # on CD Sleeve)
- Compatible with generators
- Strong EMI compatibility, no EMI to load
- Protection against Surge, Over / Under voltage

Specifications

Power: 510W

Noise: <45db (1 metre)

Temperature: 0 - 40°C

Humidity: 20% - 90% (Non-condensing)

Input - Phase: Single & GND

Input - Voltage Range: 162 - 295VAC

Input Frequency: 50 / 60Hz ± 10%

Output - Voltage Range: 230VAC+/-10%

Output - Wave Form: Sine Wave (AC Mode) Square Wave (Inverter)

Output Frequency: 50 / 60Hz ± 1% (Battery Mode)

Output - Crest Factor: 3:1

Output Transfer Time: ≤ 6ms

Protection Energy Rating: 320 Joules instantaneous response

Protection Test Standard: IEEE 587 Cat. A & B

Protection LAN: RJ45 Surge protection

Noise Filtering - EMI / RFI: Full time suppression

Input Plug: 1 x UK Plug

Output Socket: 1 x UK Socket + 3 x IEC 320 C13

Tel / Modam: 2 x RJ45

Interface: 1 x USB

Battery - Type: Sealed Lead-acid maintenance free

Battery - Qty: 12V8AH x 1

Battery - Recharge Time: 90% capacity after 8 hours

Battery - Backup Time: 15-20 minutes (dependent on load)

Unit Width (Inc. Brackets): 483mm

Unit Depth (Inc. Handles): 350mm

Packaging Type: EPE Foam

EPE Foam (Thickness): 38.81mm

General Specifications

Manufacturer: RACK 850VA

Part Number:

EAN Number: 5055492407979

Has Mains Plug: No

Colour: Black

Rackmount UPS

What's In The Mains Cable

Box: USB Cable

Software

Manual

Unit (Product)

Dimensions 438mm x 88mm x 312mm (W x H x D)
(mm):

Packaging

Dimensions 525mm x 189mm x 402mm (W x H x D)
(mm):

Net Weight 8.7 KGs
(KGs):

Gross Weight 9.8 KGs
(KGs):