



## Main

Range of product	OsiSense XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	Flat form 40 x 40 x 15
Memory capacity	3.408 kB
Associated smart antenna	XGCS
[Sn] nominal sensing distance	1.30 in (33 mm) XGCS49 1.89 in (48 mm) XGCS89 1.89 in (48 mm) XGCS85
Outer dimension	40 x 40 x 15 mm
Quantity per set	Set of 1
Read time	9.25 + 0.375 x (number of 16-bit words) ms
Write time	13 + 0.8 x (number of 16-bit words) ms
IP degree of protection	IP68
Fixing mode	By screws By clips

## Complementary

Memory type	EEPROM
Memory operation	Read/write
Number of read cycles	Unlimited
Number of write cycles	100000 -13...158 °F (-25...70 °C) 2500000 86 °F (30 °C)
Maximum linear speed with "auto read/write function"	10.17 Ft/S (3.1 m/s) XGCS49 read a serial number 4.59 Ft/S (1.4 m/s) XGCS49 read a word 8.86 Ft/S (2.7 m/s) XGCS89 read a word 8.86 Ft/S (2.7 m/s) XGCS85 read a word 3.94 Ft/S (1.2 m/s) XGCS49 read or write 10 words 15.75 Ft/S (4.8 m/s) XGCS89 read a serial number 5.91 Ft/S (1.8 m/s) XGCS89 read or write 10 words 15.75 Ft/S (4.8 m/s) XGCS85 read a serial number 5.91 ft/s (1.8 m/s) XGCS85 read or write 10 words
Data retention time	10 year(s)
Mounting location	Possible on metal support
Material	PBT (polybutylene terephthalate)
Net Weight	0.07 lb(US) (0.031 kg)

## Environment

Standards	ISO 14443
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	2 mm 5...29.5 Hz)EN 60068-2-6 7 gn 29.5...150 Hz)EN 60068-2-6
Shock resistance	30 gn 11 ms EN 60068-2-27
IK degree of protection	IK02 EN 50102

## Ordering and shipping details

Category	22491 - SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	00785901601883
Nbr. of units in pkg.	1
Package weight(Lbs)	0.09 lb(US) (0.04 kg)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.54 in (9 cm)
Package 1 width	0.79 in (2 cm)
Package 1 Length	2.36 in (6 cm)

## Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Dimensions


Updatable Code Electronic Tags



(1) For CHC type screws


Minimum Mounting Distances

Distance Between Tags



XGCS4901201 smart antenna (format 40)		XGCS8•• smart antennas (format 80)	
e1	e2	e1	e2
20	10	70	40

Minimum Mounting Distances in a Metal Structure



(e) ≥ 20 mm.