



Wiha. Premium Werkzeuge für Profis.

**7042 DR**

**DuraBit, Pozidriv, Style E 6.3.**



- Material High grade chrome-vanadium steel, through hardened.
- Geometry Patented torsion zone to prevent premature breaking of the bit when under stress.
- Coating Hard-metal coating, extremely wear-resistant.
- Drive DIN 3126, ISO 1173, Style E 6.3.
- Application For effortless, safe working in demanding industrial applications and on delicate surfaces.
- Extra Non-corrosive coating.  
Extremely wear-resistant Dura tip with hard-metal coating grips into the screw head and prevents the bit from slipping.

Order No.			
23394	PZ1	50	5
23396	PZ2	50	5
23398	PZ3	50	5

**7015 Z TR**

**Standard Bit, TORX® H, Style C 6.3.**



- Material High grade chrome-vanadium steel, through hardened.
- Drive DIN 3126, ISO 1173, Style C 6.3.
- Application For all types of screw applications in trade and industry.
- Extra Hole in the bit tip for TORX® Tamper Resistant security screws.

Order No.			



Wiha. Premium Werkzeuge für Profis.

01727	T10H	25	10
01728	T15H	25	10
01729	T20H	25	10
01730	T25H	25	10

**7013 Z**

**Standard Bit, Hex, Style C 6.3.**



Material High grade chrome-vanadium steel, through hardened.  
 Drive DIN 3126, ISO 1173, Style C 6.3.  
 Application For all types of screw applications in trade and industry.

Order No.			
01703	2,0	25	10
01704	2,5	25	10
01705	3,0	25	10

**7041 Z**

**Standard Bit, Phillips, Style E 6.3.**



Material High grade chrome-vanadium steel, through hardened.  
 Drive DIN 3126, ISO 1173, Style E 6.3.  
 Application For all types of screw applications in trade and industry.  
 Extra Overlength bits available in lengths of 70, 90, 110, 127 and 150 mm.

Order No.			
01803	PH1	70	5