

## Pneumatic spiral hose

Made of polyurethane (PU)



### Application:

For connection to compressed-air tools and compressed-air machines.

### Execution:

- With rotating brass connection parts
- With straight input and output piece (10 and 50 cm)
- Resistant to oil, petrol and acid

### Advantage:

- Perfect in combination with spring balances



<b>Art. no.</b>	<b>75051 130</b>
<b>Brand</b>	RED ROOSTER
<b>Manufacturer Part Number</b>	PT-02550SJ
<b>Hose length</b>	10 m
<b>Outer diameter of hose</b>	9.5 mm
<b>Inner hose diameter</b>	6.5 mm
<b>Connection thread</b>	G 1/4 inch
<b>Max. operating pressure</b>	10 bar
<b>Min./max. temperature conditions</b>	-20 to 80 °C
<b>Gross Weight</b>	0.578 kg
<b>Product Group</b>	7AF

### EAN

8717981059492