


ALLNET Sunlight Wall Display 27 Zoll High Brightness FullHD, Signage

[>>> Zum Shop-Artikel](#)



EAN CODE



ALLNET Signage Display 27 Zoll FullHD Wanddisplay, Showroom Series FullHD

Maximale Auflösung: 1920*1080;
Betrachtungswinkel: 89/89/89/89;Helligkeit: 1000 nits
Wandmontage
Farbe Schwarz

Achtung Kaltgerätekabel muss extra bestellt werden.!

System	CPU	RK3588S2 Quad core cortex A55+Quad core cortex A76
	RAM	8GB
	Internal memory	64GB
	Operation system	Android 13
Display	Panel Size	27" TFT
	Panel Type	IPS
	Resolution	1920x1080 16:9
	Display Colors	16.7M Colors
	Color Gamut	sRGB 99%
	Display mode	Normally black
	Viewing angle	85/85/85/85(L/R/U/D)
	Contrast ratio	3000:1

	Luminance	1000 cdm2
	Aspect Ratio	16:9
	Response Time	14ms
	Back-light Type	LCD
Network	WiFi	802.11b/g/n/a/ 2,4/5GHz
	Ethernet	100M/1000M
	Bluetooth	Bluetooth 5.0
Interface	Power Jack	IEC C13
	MIC IN	no
	Earphone Output	no
	Type-c	yes
	SIM Slot	no
	USB	Standard USB 2.0 Host
	USB	USB 3.0
	USB	USB 3.0
	RJ45	Ethernet interface
Other	Product Colors	white/Black
	VESA	no
Other Power	Speaker	40*5W*2
	NFC	no
	G-sensor	no
	Camera	no
	Language	Multi-language
	Certificates	CE/FCC
	Power Type	Adapter
	Input Voltage	230V via internal power supply unit (12V connection not sufficient)
	Power consumption	=60W
Surrounding	Storage Temperature	-20°C---60°C
	Working Temperature	0°C---45°C 20~80%RH
	Adapter	interne PSU

Farbe Schwarz

Zubehör



Art.-Nr.: 235554
Herst.-Nr.: Sunlight Wall 270

Art.-Nr.	Name
87435	Netzkabel 230V Schutzkontakt CEE7(Stecker)->Kaltgeräte IEC-C13(Buchse), 2m, Black, Synergy 21,
137095	Netzkabel 230V Schutzkontakt CEE7(Stecker)->Kaltgeräte IEC-C13(Buchse), 1m, Black, Synergy 21,
140159	Netzkabel 230V Schutzkontakt CEE7(Stecker)->Kaltgeräte IEC-C13(Buchse), 3m, Black, Synergy 21,
137094	Netzkabel 230V Schutzkontakt CEE7(Stecker)->Kaltgeräte IEC-C13(Buchse), 0,5m, Black, Synergy 21,