

Dial gauge

TESA



Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

Execution:

- Housing: Metal
- Clamping shank: Stainless steel
- Measuring pin: Stainless steel
- Clamping shank: Dia. 8 mm
- Dial gauge with gauge slide dia. 3.175 mm, mounted
- Clockwise
- Thread for gauge slides: M2.5

Advantage:

- Rotating dial

Delivery:

In box



Art. no.	33151 050
Brand	TESA
Manufacturer Part Number	01419080
Length measuring range	3.5 mm
Scale value	0.01 mm
Measurement travel of one pointer revolution	0.5 mm
Outer diameter	28 mm
Shock protection	No
Material of outer ring	Metal
IP protection class	IP 40
Measurement force	0.8 N
Calibration Group	CE
Gross Weight	0.077 kg
Product Group	362

EAN

7630041151770