

3D articulated measuring stand, μ -line

815 MF



Application:

Highest stability and rigidity for μ -precision measurements

Execution:

- Mechanical, maintenance-free central clamping
- Dovetail mount and holder \varnothing 8 mm
- Strong adhesive magnet with prismatic base

Advantage:

- Simple, quick operation
- High degree of manoeuvrability, exact positioning
- Precision adjustment with high repeat accuracy for measurements in the μ -range

Delivery:

Without precision pointer



Art. no.	34060 233
Brand	MAHR
Manufacturer Part Number	4420388
Height	444 mm
Operation radius	330 mm
Adherence strength	1000 N
Base size	73 x 50 x 55 mm
Max. shaft diameter	120 mm
Gross Weight	2.580 kg
Product Group	305

EAN

4059192061784