

9013 M pneumatic impact screwdriver

Tightening torque 1085 Nm



Application:

For heavy screwing work

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- Handle insulated against cold
- Exhaust air discharged downwards through the handle

Delivery:

Includes coupling plug



Art. no.	75065 041
Brand	HAZET
Manufacturer Part Number	9013M
Model	9013M
Suitable for screw	M32
Max. tightening torque	1085 Nm
Max. releasing torque	1890 Nm
Max. idle speed	7300 rpm
Air consumption	153 l/min
Tool holding device	3/4-inch external square
Hammer mechanism system	Twin hammer mechanism
Length	188 mm
Connection thread	IT 3/8 inch
Inner hose diameter	10 mm
Operating pressure	6.3 bar
Sound-pressure level	104
Weight	2.1 kg
With right/left-hand rotation	Yes
Gross Weight	2.442 kg
Product Group	738

EAN

4000896212347