



PLUG-IN RELAY COMPLETE UNIT AC 115V, 4 CO CONTACT LED MODULE RED STANDARD PLUG-IN SOCKET SCREW TERMINAL 3.5 MM PINNING

Figure similar

**General technical data:**

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• with AC		
— at 50 Hz Rated value		
— minimum	V	115
— maximum	V	115
— at 60 Hz Rated value		
— minimum	V	115
— maximum	V	115
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		4
Operating current of the auxiliary contacts		
• at DC-13		
— at 24 V	A	6
• at AC-15		
— at 230 V	A	4
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable

#### Mechanical data:

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	28
Height	mm	72
Depth	mm	74

#### Certificates/ approvals:

General Product Approval

other



[Declaration of Conformity](#)

#### Further information

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT5A5S15>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT5A5S15>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZS:PT5A5S15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT5A5S15&lang=en)

last modified:

15.01.2015