

Quick coupling plug NPHS-S6-M-BC9

Part number: 8059265

FESTO



Data sheet

Feature	Value
Nominal size	7 mm
Short type code	NPHS NPHS
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	17 g
Pneumatic connection, port 1	For plug-in nipple I.D. 9 mm For plug-in nipple I.D. 9 mm
Note on materials	RoHS-compliant