

Pneumatic spiral hose

Made of polyamide



Application:

For connection to compressed-air tools and compressed-air machines.

Execution:

- With special fitting connections at both ends
- Suitable for water and air
- Max. pressure: 10 bar
- Max. temperature: 90°C
- For a clearly organised workplace
- For reducing the risk of accidents



| | |
|---------------------------------|------------------|
| Art. no. | 75052 010 |
| Brand | PREVOST |
| Manufacturer Part Number | SPIC 62 |
| Hose length | 2.5 m |
| Outer diameter of hose | 8 mm |
| Inner hose diameter | 6 mm |
| Connection thread | G 1/4 inch |
| Max. operating pressure | 10 bar |
| Gross Weight | 0.232 kg |
| Product Group | 758 |

EAN

3660058027908