

Wet/dry vacuum cleaner Aero Inox 21-01PC INOX

Power consumption 1250 watt



Application:

Handy and robust vacuum cleaner – ideal for small cleaning tasks in workshops

Delivery:

With 1.8 m suction hose (dia. 32 mm), hand-held tube with suction regulation, extension tube, joint and floor nozzle, universal nozzle, filter element and fleece filter bag



Art. no.	75520 012
Brand	NILFISK
Manufacturer Part Number	107406602
Model	21-01 PC INOX
Power input	1250 W
Max. air delivery volume	3600 l/min
Material of bins	Stainless steel
Underpressure	210 mbar
Bin capacity	20 l
Sound-pressure level	64 dB
Weight	8.5 kg
Cable length	5 m
Filter cleaning	Semi-automated
With device connector	No
With antistatic system	No
With automatic shut off	No
With accessory tray	Yes
With soft start	No
Length x width x height	390 x 400 x 525 mm
With speed control	No
Inner hose diameter	32 mm
Hose length	1.8 m
Nominal voltage	230 V
Gross Weight	10.000 kg
Product Group	7AJ

EAN

5711145158840