

## Angular milling cutter set with shank 90° 25x90 mm

Includes 20x APMT T003PDER-M OHC4635

**ORION**<sup>®</sup>

### Execution:

- Angular milling cutter 90° with shank
- for indexable milling inserts AP..1003..
- Soft cutting by positive installation position of the reversible tip
- For groove milling and circumferential milling
- Smooth milling behaviour of the tools

### Advantage:

- One set for a wide variety of applications
- Axial run-out max. 0.03 mm
- Concentricity max. 0.03 mm
- precise 90° angular milling

### Delivery:

1x carrier 16017037 + 20x indexable inserts 16109145



<b>Art. no.</b>	<b>16017043</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16017043
<b>Cutting edge diameter</b>	25 mm
<b>Clearance length</b>	49 mm
<b>Length</b>	105 mm
<b>Shank diameter</b>	25 mm
<b>max. ap</b>	8 mm
<b>Number of cutting edges</b>	4 PCS
<b>Number of cutting inserts</b>	4 PCS
<b>Gross Weight</b>	0.497 kg
<b>Product Group</b>	148

### EAN

4053625626328