

**Application:**

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

**Execution:**

- Housing: Metal
- Clamping shank: Stainless steel
- Measuring pin: Stainless steel
- Clamping shank: Dia. 8 mm
- Dial gauge with gauge slide dia. 3.175 mm, mounted
- Clockwise
- Thread for gauge slides: M2.5

**Advantage:**

- Rotating dial, adjustable tolerance marks

**Delivery:**

In box



<b>Art. no.</b>	<b>33151 040</b>
<b>Brand</b>	TESA
<b>Manufacturer Part Number</b>	01419054
<b>Length measuring range</b>	1 mm
<b>Scale value</b>	0.001 mm
<b>Measurement travel of one pointer revolution</b>	0.2 mm
<b>Outer diameter</b>	58 mm
<b>Shock protection</b>	Yes
<b>Material of outer ring</b>	Metal
<b>IP protection class</b>	IP 40
<b>Measurement force</b>	1.4 N
<b>Calibration Group</b>	CE
<b>Gross Weight</b>	0.240 kg
<b>Product Group</b>	362

**EAN**

7630041151848