

Slides DS 5321 EC, Width 19.1 mm, to 100 kg, Stainless Steel, Full Extension

Material: Stainless steel 1.4301 (AISI 304).




Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Self Close on the last 45mm of travel.
 - Suitable for drawers up to 1000mm wide at high load.
 - Service life 80,000 cycles.
 - Temperature range: +0°C to +40°C. Storage: -20°C to +80°C.
- Opening force 25N +/- 5N.



Accuride

Ordering details: e.g.: Prod. No. 64904140, Slides DS 5321 EC



Product No. per Pair	Slide Length mm	Travel ±3 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	Load Rating ¹⁾ per Pair kg	Weight per Pair kg
649 041 40	400	388	160	192	-	-	128	160	-	288	65 / 55	1,99
649 041 45	450	450	160	192	256	-	128	160	-	320	65 / 55	2,27
649 041 50	500	500	192	224	-	-	160	192	-	384	70 / 60	2,57
649 041 55	550	550	192	224	320	352	160	192	-	416	85 / 72	2,87
649 041 60	600	600	256	288	384	416	192	256	-	480	100 / 85	3,18
649 041 70	700	700	288	320	448	480	256	288	512	576	100 / 85	3,79
649 041 80	790	800	352	384	544	576	320	352	416	672	90 / 75	4,42

¹⁾ Drawer width 450mm / 1000mm.

Note

Recommended mount: M5 countersunk / 6mm countersunk euro screw.

Use all mounting positions to achieve the max. load rating.

Optional clip-on brackets for bottom or platform mounting on request.

Attention: Vertical mounting only.

Selection Tool
on the Internet at www.maedler.de
in the section **MÄDLER®-Tools**