

LED cold light source F3000

With very good light output of up to 640 lm

▼ PHOTONIC

Application:

Fibre optic light source impresses with its excellent light output. Ideal for stereomicroscopic and endoscopic inspection tasks requiring good illumination. Due to the low heat generation, also suitable for heat sensitive objects.

Execution:

- Robust metal housing
- Infinitely variable brightness regulation
- ESD connector
- Electronic shutter function
- Remote control via USB and foot switch (toggle standby, toggle presets, dimming)
- All settings (brightness/shutter/strobe parameters) can be easily configured

Advantage:

- High light density over a small surface
- infinite brightness regulation from 1 - 100% (flicker-free)
- Intelligent fan control for minimal noise emission
- Brightness, shutter/strobe parameters individually configurable



Art. no.	41613 637
Brand	PHOTONIC
Manufacturer Part Number	10060.1 + ELN-3.001
Model	F3000
Lamp type	LED
Colour temperature	5800 K
ESD bush	Yes
Life time of illuminant	30000 h
Input voltage	12 V/DC
Min./max. nominal voltage	100 / 240 V/DC
Gross Weight	5.800 kg
Product Group	412