






# TJ-70/85 ThermoJet Handpieces & Tips




## TJ-70 ThermoJet/Replacement Parts & Handpiece Tips

HANDPIECE	DESCRIPTION	PART NUMBERS
	TJ-70 ThermoJet SensaTemp Handpiece	7023-0002-P1
	Heater assembly	6010-0084-P1
	Handle Kit	6993-0140-P1
	Hardware Kit	6993-0189-P1
	Gender Bender Adaptor (Allows SensaTemp Handpieces to be used on IntelliHeat power sources)	6993-0278-P1
	SX Tool Stand (Available November 2007)	6019-0082-P1

TIP	DESCRIPTION	TIP SIZE A x B	PART NUMBERS
	Small, Straight, Single Jet Tip	0.060" I.D.	1121-0366-P1
	Small, Curved, Single Jet Tip	0.060" I.D.	1121-0338-P1
	SOIC Tip (dual-jet)	A = 4.32mm (0.17")	1121-0330-P1
	Flat End Tip	A = 7.11 mm (0.28") B = 1.88mm (0.074")	1121-0365-P1
		A = 6.10mm (0.24") B = 1.88mm (0.074")	1121-0371-P1

## TJ-85 ThermoJet/Replacement Parts & Handpiece Tips

HANDPIECE	DESCRIPTION	PART NUMBERS
	Heater Retaining Nut	1410-0122-P5
	Flared Ring	1500-0074-P5
	Heater Assembly	6010-0143-P1
	TJ-85 Handpiece IntelliHeat	6010-0153-P1
	TJ-85 Kit IntelliHeat	6993-0270-P1
	TJ-85 Cubby (Available November 2007)	6019-0081-P1
	TJ-85 Handpiece SensaTemp	6010-0142-P1
	TJ-85 Handpiece Kit SensaTemp	6993-0247-P1

TIP	DESCRIPTION	TIP SIZE A x B	PART NUMBERS
	Straight Nozzle	0.06" Inner Diameter	1259-0129-P1
	Curved Nozzle	0.06" Inner Diameter, Bent 60 Degrees	1259-0130-P1
	Flat Nozzle	0.24" X 0.074" Inner flow Dimensions	1259-0131-P1