



RE120-LF

- Epoxy fibre-glass FR4 1.50 mm
- Single-sided 35 µm Cu
- Hot air leveling (HAL-leadfree)
- Hole spacing 2.50 x 2.50 mm
- 37 x 58 soldering pads 2.20 mm Ø
- Hole diameter 1.00 mm
- Connector 31-channel DIN 41617
- Size 100 x 160 mm




RE120-LF

- Epoxydglashartgewebe FR4 1,50 mm
- Einseitig 35 µm Cu
- Heißverzinnt (HAL-leadfree)
- Lochraster 2,50 x 2,50 mm
- 37 x 58 Lötinseln 2,20 mm Ø
- Lochdurchmesser 1,00 mm
- Steckverbinder 31-polig DIN 41617
- Größe 100 x 160 mm



RE120-LF

- Fibre de verre époxyde FR4 1,50 mm
- Simple face 35 µm Cu
- Étamé à chaud (HAL-leadfree)
- Pas 2,50 x 2,50 mm
- 37 x 58 îlots de brasage 2,20 mm Ø
- Perforation 1,00 mm Ø
- Pour connecteur 31-pôles DIN 41617
- Dimensions 100 x 160 mm



RE120-LF

- Fibra de vidrio epoxídica FR4 1,50 mm
- Por un lado 35 µm de Cu
- Estañado en caliente (HAL-leadfree)
- Trama de agujeros 2,50 x 2,50 mm
- 37 x 58 nodos de soldadura 2,20 mm Ø
- Diámetro de los agujeros 1,00 mm
- Conector enchufable 31-polos DIN 41617
- Tamaño 100 x 160 mm