

HEINE K180® Fiber Optic (F.O.) Otoscope

The standard, all around Fiber Optic Otoscope



Otoscope with Fiber Optic (F.O.) illumination constructed of light, high-impact polycarbonate and **3x magnification** scratch-resistant acrylic viewing window. Otherwise technically identical to the BETA200 F.O. Otoscope.

- Fiber Optic (F.O.) illumination
- Polycarbonate construction

K180 F.O. Otoscope	2.5V	3.5V
with 4 reusable tips, without handle	B-001.11.551	B-002.11.551
same, without tips, without handle	B-001.11.550	B-002.11.550
XHL Xenon Halogen spare bulb	X-001.88.077	X-002.88.078

HEINE K180® Fiber Optic (F.O.) Diagnostic Sets

Set complete with: **K180 Fiber Optic (F.O.) Otoscope**
 1 set (4 pcs.) of reusable tips (B-000.11.111)
 soft pouch



K180 F.O. Otoscope Sets	2.5V	3.5V (NiMH)	3.5V
BETA battery handle	B-181.10.118		
BETA R rechargeable handle for mains socket		B-181.20.376	B-181.27.376
BETA TR rechargeable handle with plug-in transformer		B-181.20.384	B-181.27.384
BETA NT rechargeable handle and NT300 charger		B-181.20.420	
BETA L rechargeable handle and NT300 charger			B-181.29.420

Set complete with **K180 Ophthalmoscope, K180 Fiber Optic (F.O.) Otoscope**
 1 set (4 pcs.) of reusable tips (B-000.11.111)
 hard case



K180 Combined Diagnostic Sets	2.5V	3.5V (NiMH)	3.5V
BETA battery handle	A-279.10.118		
BETA R rechargeable handle for mains socket		A-279.20.376	A-279.27.376
BETA TR rechargeable handle with plug-in transformer		A-279.20.384	A-279.27.384
BETA NT rechargeable handle and NT300 charger		A-279.20.420	
BETA L rechargeable handle and NT300 charger			A-279.29.420

: Rechargeable handle with charge status display in the bottom insert.