

Eccentric Quick Clamps · with female thread

23390.0301

Product Description

For quick and easy clamping and releasing of workpieces.
When using the "adjustable" design (picture 2) the lever position can be moved.



Material

Support washer

- Thermoplastic POM, glass-fiber reinforced

Lever

- Zinc die-cast, plastic coated, black

Threaded part

- Stainless steel 1.4305


Inner parts

- Stainless steel 1.4305

Adjusting nut

- Stainless steel 1.4305


Drawing



Order information

Dimensions										Stroke s at 90° lever position [mm]	🌡️ max. [°C]	📦 [g]	Art. No.
l	d ₁	d ₃	d ₄	h ₂ max.	Regulating- range h ₃ min.	b	t ₁	t ₂ min. in clamping position	[mm]				
with female thread, adjustable – picture 2, stainless steel													
63	M6	16	19	16.4	1.5	16	13	3	0.75	80	65	23390.0301	

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 10.06.2022

Does not contain Proposition 65 substances

No Proposition 65 substances included
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.