

Boring bar AMI left

For internal recessing and copy turning using AD and AE cutting inserts

ATORN

Application:

For recessing and copy turning, internal

Execution:

- Precision-manufactured steel support, nickel-plated and hardened with clamping element



Art. no.	17673 786
Brand	ATORN
Manufacturer Part Number	12371019
Suitable for knife width	4 mm
Shank diameter	32 mm
Programming size	11 mm
Plunge depth	11 mm
Length	250 mm
Immersion depth	11 mm
Clamping surface height	31 mm
Adjustment rate via centre	27.5 mm
Min. bore diameter	41 mm
Tool design	Left
Gross Weight	1.421 kg
Product Group	1FF

EAN

4050293740431