



NH-Schmelzeinsätze 500V gL/gG

Standardausführung und Ausführung I

HRC Fuse links 500V gL/gG

Design Standard and I

Typ	Nennstrom	Best-Nr.	Pckg./ Stck.	Gewicht kg/%	Nennstrom	Best-Nr.	Pckg./ Stck.	Gewicht kg/%	Abbildung
Größe C 00	2 A	0006	3/120	12	32 A	012501	3/120	12	
	4 A	0007	3/120	12	35 A	012601	3/120	12	
	6 A	012001	3/120	12	40 A	012701	3/120	12	
	10 A	012101	3/120	12	50 A	012801	3/120	12	
	16 A	012201	3/120	12	63 A	012901	3/120	12	
	20 A	012301	3/120	12	80 A	013001	3/120	12	
	25 A	012401	3/120	12	100 A	013101	3/120	12	
Größe 00	125 A	0132	3/90	16	160 A	0133	3/90	16	
Größe C 00 isoliert	6 A	0088	3/120	12	35 A	0094	3/120	12	
	10 A	0089	3/120	12	40 A	0095	3/120	12	
Ausführung I 	16 A	0090	3/120	12	50 A	0096	3/120	12	
	20 A	0091	3/120	12	63 A	0097	3/120	12	
	25 A	0092	3/120	12	80 A	0098	3/120	12	
	32 A	0093	3/120	12	100 A	0099	3/120	12	
	Größe 00 isoliert	125 A	0100	3/90	20	160 A	010001	3/90	20
Größe 00/125 + 160 A nach VDE 0636/21									
Größe 0	6 A	0101	3/60	21	40 A	0108	3/60	21	
	10 A	0102	3/60	21	50 A	0109	3/60	21	
	16 A	0103	3/60	21	63 A	0110	3/60	21	
	20 A	0104	3/60	21	80 A	0111	3/60	21	
	25 A	0105	3/60	21	100 A	0112	3/60	21	
	32 A	0106	3/60	21	125 A	0113	3/60	21	
	35 A	0107	3/60	21	160 A	0114	3/60	21	
Größe C 1	25 A	0151	3/60	23	63 A	0156	3/60	23	
	32 A	0152	3/60	23	80 A	0157	3/60	23	
	35 A	0153	3/60	23	100 A	0158	3/60	23	
	40 A	0154	3/60	23	125 A	0159	3/60	23	
	50 A	0155	3/60	23	160 A	0160	3/60	23	
Größe 1	200 A	0148	3/30	35	224 A	0149	3/30	35	
	250 A	0150	3/30	35					
Größe 2	40 A	0165	3/24	39	200 A	0172	3/24	39	
	50 A	0166	3/24	39	224 A	0173	3/24	39	
	63 A	0167	3/24	39	250 A	0174	3/24	39	
	80 A	0168	3/24	39	300 A	0175	3/24	54	
	100 A	0169	3/24	39	315 A	0176	3/24	54	
	125 A	0170	3/24	39	355 A	0177	3/24	54	
	160 A	0171	3/24	39	400 A	0178	3/24	54	
Größe 2/300 A nach VDE 0636/21									
Größe 3	315 A	0181	3/18	55	425 A	0184	3/18	110	
	355 A	0182	3/18	55	500 A	0185	3/18	110	
	400 A	0183	3/18	55	630 A	0186	3/18	110	
Alle Stromstufen nach VDE 0636/21									
Größe 4	630 A	018601	1	216	1000 A	018603	1	216	
	800 A	018602	1	216	1250 A	018604	1	216	
Größe 4a	630 A	018605	1	217	1000 A	018607	1	217	
	800 A	018606	1	217	1250 A	018608	1	217	