



Yuasa Technisches Datenblatt

Yuasa YBX3005 - YBX3000 SMF Batterien

Leistung

Spannung	12V
Kapazität 20 Std (vorgegeben)	60Ah
Kaltstartstrom (A) EN1	450A

Abmessungen

Länge	232mm
Breite	175mm
Höhe	225mm

Maße und Gewichte

Durchschnittliches Gewicht inkl. Säure	14.9kg
Gewicht (trocken)	-
Säure Volumen	-



Gehäuseeigenschaften

Gehäusotyp	JIS D23
Batteriehälter	N
Ladezustandsanzeige	✓
Tragegriffe	✓
Entgasung	✓
Semi Traktionseigenschaften	-
Deckel Typ	SMF doppelwandige Deckelkonstruktion

Technologie

Flammschutz	✓
Technologie	Ca/Ca
Separator	PE
VDA Überroll Test	✓
Ladestrom	4A


Anschlusspol Typ

T1

Standard DIN Post



Zellenanordnung



Batteriehälter



Ausstellungsdatum: 10/08/2018 - E&EO



Yuasa Technical Data Sheet

Yuasa YBX3005 - YBX3000 SMF Batteries

Performance

Voltage	12V
Capacity (20-hour)	60Ah
Cold Cranking Amps (EN1)	450A

Dimensions

Length	232mm
Width	175mm
Height	225mm

Weights & Measures

Mean Weight with Acid	14.9kg
Dry Weight	-
Acid Volume	-



Container Features

Case Type	JIS D23
Hold Down	N
State of Charge Indicator	✓
Handles	✓
End Venting	✓
Semi-Traction Features	-
Lid Type	SMF Double Lid


Technology

Flame Arrestor	✓
Technology	Ca/Ca
Separator	PE
VDA Roll Over Test	✓
Recommended Charge Rate	4A


Terminal Type

T1

Standard DIN Post



Cell Assembly Layout



Battery Hold-down



Data Sheet generated on 10/08/2018 - E&OE