

# HUBER+SUHNER® DATA SHEET

## Within Series Adapter: 34\_SMA-50-0-100/111\_N



### Description

Bulkhead adaptor jack/jack  
SMA-26.5GHz jack (female) / SMA-26.5GHz jack (female)

Interface standards  
SUHNER-SMA-26.5GHz



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 26.5 GHz  
Electrical Length 25.72 mm +/- 0.1

#### Mechanical Data

Number of matings 500  
Weight 0.0041 kg

#### Environmental Data

Operating Temperature -65 °C to 125 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts (SMA-26.5GHz)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Copper Beryllium Alloy
Insulator	PFA / PTFE

##### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

##### Piece Parts (SMA-26.5GHz)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Copper Beryllium Alloy
Insulator	PFA / PTFE

##### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

### Related Documents

Mounting hole DOU-00008731

### Ordering Information

Single package 34\_SMA-50-0-100/111\_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**