



Description:

Spigots ECO fitted with 3/4" outer thread for controlled emptying of liquid from barrels and jerrycans, natural-coloured

- made of fracture-proof and food-safe polyethylene with sleeve connection for a hose
- very resistant to acids, alkalis and other chemicals
- with pipe thread R 3/4"
- natural-coloured with white PE foam seal
- without ventilation
- Pressure resistance up to 0.4 bar
- resistant to temperature: -20°C to +70°C
- Run-out speed > 1.5 L/min
- Connection area outside diameter = 19 mm or 3/4"

Information:

Article

Articlenumber	560000
GTIN	4007228560008
Customs tariff	39174000
Packaging Unit (PU)	5

Colour	natural
Weight (kg)	0,03

Outer packaging

Content in pieces	5
L x B x H (mm)	515 x 297 x 314

Gross weight unit (kg)	0,15
------------------------	-------------

Pallet

Number of boxes	36
Number of layers	6
L x B x H (m)	1,2 x 0,8 x 2,034

Carton per layer	6
Weight (kg)	74,0