

LED workstation lamp FLEXI 90°

With and without dimmer



Execution:

- LED module up to 450 lumen, glare- and flicker-free, colour temperature: daylight white, approx. 5500 Kelvin
- Flicker-free and low reflection, 120-degree uniform illumination, with wall power supply unit. 24 V supply.
- Rubber-coated 66-mm magnetic base with adhesive force of 180 N
- Cover made of acrylic, total length 600 mm, lamp head 65 mm
- Chip life min. 50,000 hours.
- Ref. no. 141: No dimmer
- Ref. no. 143: With dimmer (continuously variable)

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



Art. no.	56879 143
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/46D
Power rating	4.5 W
Arm length	500 mm
IP protection class	IP 65
Dimmable	Yes
Gross Weight	1.092 kg
Product Group	5ID

EAN

4260131238574