

## J.17 J - 3/8" metric 12-point sockets



### Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

A [mm]:	17
d [mm]:	21,7
d1 [mm]:	23,4
L [mm]:	30
L1 [mm]:	13,0
12-Point [mm]:	12
[g]:	52

