

Slides DZ 2720, Width 9.5 mm, to 20 kg, 3/4 Extension

Material:

Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Cold-rolled steel, zinc-plated.

Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Compact profile.
- Low height.
- Service life 80,000 cycles.
- Temperature range: -20°C to +70°C.



Accuride

Ordering details: e.g.: Prod. No. 649 019 20, Slides DZ 2720



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	Load Rating per Pair kg	Weight per Pair kg
649 019 20	200	145,2	-	-	128	160	13	0,30
649 019 25	250	182,5	-	-	160	192	15	0,36
649 019 30	300	219,8	-	128	224	256	18	0,44
649 019 35	350	257,1	128	160	256	288	20	0,52
649 019 40	400	294,4	160	192	320	352	20	0,58
649 019 45	450	331,7	192	224	352	384	20	0,66
649 019 50	500	369,0	224	256	416	448	18	0,74

Note

Recommended mount: M4 screw.

Max. head. height 2,5mm/Ø9,6mm.

Use all mounting positions to achieve the max. load rating.

The load capacity was tested with a rail spacing of 450 mm.

Selection Tool
on the Internet at www.maedler.de
in the section **MÄDLER®-Tools**