

Lever chain hoist with ratchet tool

Made of sheet steel

Application:

For tensioning, hoisting, pulling and tying down.

Execution:

- Robust sheet steel housing (powder-coated)
- Galvanised load chain in line with DIN EN 8 18-7 (quality class T)
- Free-chaining feature for rapid passage of the unloaded chain
- Automatic operation, fully enclosed load pressure brake
- Reinforced hook protection

Advantage:

- Rapid passage of unloaded chain
- Suitable in industrial settings for lifting, pulling and tensioning
- Can also be used as a lashing device on lorries
- Vibration-resistant brakes
- Easy-release brakes, particularly when used as a lashing device



Art. no.	77158 080
Load-carrying capacity	800 kg
Nominal chain thickness	15.8 mm
Chain diameter	5.6 mm
Stroke force at nominal load	25 daN
Length of lever	245 mm
Stroke height per lever revolution	29 mm
Lift height	1500 mm
Min. hook spacing	280 mm
Number of load chains	1 PCS
EN standard	8 18-7
Gross Weight	7.100 kg
Product Group	7EH

EAN

4036475000296