

Angular milling cutter HSSE Co 5

ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery



Art. no.	15815 140
Brand	ORION
Manufacturer Part Number	15815140
Cutting material	HSSE Co5
Type	N
Number of cutting edges	10 PCS
Chamfer angle	60 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	25 mm
Width of cutting edge	10 mm
Immersion depth	22 mm
Length	67 mm
Shank diameter	12 mm
Form	D
fz steel 700	0.06 mm
Gross Weight	0.091 kg
Product Group	106

EAN

4039247098217