



2DI 24VDC LC COM CONTROL MODULE FOR ET200S HIGH FEATURE STARTER FOR ET 200S FAILSAFE STARTER FOR LOCAL INPUT FUNCTIONS OR F. MANUAL OPERATION WITH COM INTERFACE FOR PC CABLE 6ED1057-1AA00-0BA0

General technical data:

Product designation		Control module 2DI 24 V DC COM
Product description		digital input module with two inputs for local motor starter functions for front mounting
Mounting height	mm	45
Installation width	mm	23.8
Installation depth	mm	23
Type of connectable conductor cross-section		1x (0.14 ... 2.5 mm ²), acc. to IEC 60947 2x (0.14 ... 1)
<ul style="list-style-type: none"> • solid • finely stranded with core end processing • for AWG conductors <ul style="list-style-type: none"> — solid — stranded 		1x (18 ... 22) 1x (18 ... 22)
Number of digital inputs		2
Ambient temperature		
<ul style="list-style-type: none"> • during storage • during operation 	°C	0 ... 60 -40 ... +80

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>


Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19030CH20>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RK19030CH20/all>

-X1



-X1



last modified:

15.01.2015