



**87**

**85 mm Standard Central Nut  
Adjustable Wrench with Phosphate  
Finish 770 mm**

**PRODUCT DETAILS**

- Large size and wide opening
- Head angle 22.5° provides better accessibility
- Laser scale in mm for pre-adjusting and accurate measurement
- High-performance alloy steel forged in single piece
- Phosphate finish, precision-hardened and anti-corrosion treated
- Right turning screw
- Standards: ISO 6787, DIN 3117, ASME B107.8-2003 and BS 6333
- Industrial pack
- Better accessibility with 22.5° angled heads
- Greater leverage due to the long handles
- Ultimate strength through precision hardening and high-performance alloy steel



**PRODUCT ATTRIBUTES**

Product							
<b>87</b>	770 mm	30 in	85 mm	31 mm	33 mm	76 mm	5700 g

**Follow the Fish!**

